

 PRODUCT TECHNICAL DATASHEET (SCHEDA TECNICA PRODOTTO)		rev. 2.0	
		04/10/2017	
		DATASHEET CODE (CODICE SCHEDA)	
		785505336	
TYPE OF UNIT		UNIT PART NR (CODICE MACCHINA)	
CCE6201 1700 WT CE STD		42130175001	
WEIGHT (MASSA) [Kg]	NOISE LEVEL (RUMORE) [Db]	COLOUR (COLORE)	PED CATEGORY (CATEGORIA PED)
67	68 (1M-60HZ)	RAL 7035	I
AMBIENT CONDITIONS (CONDIZIONI AMBIENTE)			
MIN AMBIENT TEMPERATURE (MIN TEMPERATURA AMBIENTE) [°C]	MAX AMBIENT TEMPERATURE (MAX TEMPERATURA AMBIENTE) [°C]	MAX RELATIVE HUMIDITY (MAX UMIDITA' RELATIVA) [%]	
15	45	80	
REFRIGERATION CIRCUIT (CIRCUITO FRIGORIFERO)			
COOLING CAPACITY (POTENZA DISSIPATA) [Kw]	REFRIGERANT GROUP (GRUPPO REFRIGERANTE)	REFRIGERANT TYPE (TIPO GAS)	REFRIGERANT CHARGE (CARICA GAS) [Kg]
1,7	2	R134A	0,7
MIN PRESSURE PS (MIN PRESSIONE PS) [bar]	MAX PRESSURE PS (MAX PRESSIONE PS) [bar]	MIN TEMPERATURE TS (MIN TEMPERATURA TS) [°C]	MAX TEMPERATURE TS (MAX TEMPERATURA TS) [°C]
0,5	26	-18	73
HYDRAULIC CIRCUIT (CIRCUITO IDRAULICO)			
COOLING FLUID TYPE (TIPO FLUIDO USATO)	MIN COOLING FLUID SET POINT MIN SET POINT IMPOSTABILE [°C]	MAX COOLING FLUID SET POINT MAX SET POINT IMPOSTABILE [°C]	STD FACTORY SET POINT STD SET POINT DI FABBRICA [°C]
WATER + GLYCOL 20%	10	35	18
TYPE OF PUMP (TIPO DI POMPA)	NOMINAL FLOW RATE (PORTATA NOMINALE) [L/min]	NOMINAL PRESSURE (PRESSIONE NOMINALE) 50 Hz [bar]	NOMINAL PRESSURE (PRESSIONE NOMINALE) 60Hz [bar]
PERIPHERICAL/PERIFERICA	10	2	4,6
ELECTRICAL CIRCUIT (IMPIANTO ELETTRICO)			
POWER SUPPLY (ALIMENTAZIONE) [V±10% / ph / Hz ±1%]	CONTROL CIRCUIT (CIRCUITO DI COMANDO)	ELECTRIC HEATER (RESISTENZA) [W]	SCCR [kA]
230/1/50-230/1/60	230V AC	-	5
MAX POWER INPUT [kW] - CURRENT INPUT [A] (ASSORBIMENTI MASSIMI)			
1,30 [kW] (50Hz)		1,50 [kW] (60Hz)	
7,5 [A] (50Hz)		8,5 [A] (60Hz)	
SCHEMES (SCHEMI)	HYDRAULIC DIAGRAM	ELECTRICAL DIAGRAM	
	70006-235	70010-437	
OPTIONALS INSTALLED (OPZIONI INSTALLATE)			
CONFIGURATION BASIC			
ACCESSORIES (EXTERNAL TO THE CHILLER, INSTALLATION BY CUSTOMER) ACCESSORI (INSTALLAZIONE ESTERNAMENTE AL CHILLER A CURA DEL CLIENTE)		OPTIONS OPZIONI	
		LTA-D	antivibration damper
		LTA-E	lifting eyebolt
		NFH	non ferrous hydraulic circuit
		TE	Electronic Thermostat
		WT	Water Unit