


ISO STANDARD REVISION LABEL ANSI STANDARD REVISION LABEL		Allgemeintoleranzen/ Tolerance ISO 2768-m		Maßstab/ Scale 1:3		Farbe/ Color:		Teil-Nr. Part-No. 1838000015	
Benennung/Dimension: mm [inch]		Datum/Date		Name/Name		Benennung/Description: <b>Drilling TP PWS 3152/DTS31x5</b>			
Zust/ State		Änderung/ Change No.		Datum/Date		Name		Urspr./source:	
Ers.f./substituted f.:		Ers.d./replaced by:		Ers.f./substituted f.:		Ers.d./replaced by:		Ers.f./substituted f.:	
Schutzmerk nach DIN 34 und ISO/DIS 16016: "Weitergabe und Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmerkmalregistrierung vorbehalten."		Copyright reserved of DIN 34 and ISO/DIS 16016: "The copying, distribution and utilization of this document as well as the communication for its contents to others without expressed authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or ornamental design registration."		Blatt/Blätter page/pages 1/2		REVISION 01-		DIN A2	



Drilling TP PWS 3152/DTS31x5  
18380000015 01-