

| TYPE OF UNIT | | UNIT PART NR (CODICE MACCHINA) | | | |
|---|---|--|--|---|-------------------------------|
| CCE6101 1100 WT CE STD | | 42130115006 | | | |
| WEIGHT WITHOUT FLUID (MASSA SENZA FLUIDO) [Kg] | NOISE LEVEL (RUMORE) [Db] | COLOUR (COLORE) | | PED CATEGORY (CATEGORIA PED) | |
| 67 | 68 (1M-60HZ) | RAL 7035 | | I | |
| AMBIENT CONDITIONS (CONDIZIONI AMBIENTE) | | | | | |
| MIN AMBIENT TEMPERATURE (MIN TEMPERATURA AMBIENTE) [°C] | MAX AMBIENT TEMPERATURE (MAX TEMPERATURA AMBIENTE) [°C] | MAX RELATIVE HUMIDITY (MAX UMIDITA' RELATIVA) [%] | | | |
| 15 | 45 | 80 | | | |
| REFRIGERATION CIRCUIT (CIRCUITO FRIGORIFERO) | | | | | |
| COOLING CAPACITY (POTENZA DISSIPATA) [Kw] | REFRIGERANT GROUP (GRUPPO REFRIGERANTE) | REFRIGERANT TYPE (TIPO GAS) | | REFRIGERANT CHARGE (CARICA GAS) [Kg] | |
| 1,1 | 2 | R134A | | 0,8 | |
| MIN PRESSURE PS (MIN PRESSIONE PS) [bar] | MAX PRESSURE PS (MAX PRESSIONE PS) [bar] | MIN TEMPERATURE TS (MIN TEMPERATURA TS) [°C] | | MAX TEMPERATURE TS (MAX TEMPERATURA TS) [°C] | |
| 0,5 | 26 | -18 | | 73 | |
| HYDRAULIC CIRCUIT (CIRCUITO IDRAULICO) | | | | | |
| COOLING FLUID TYPE (TIPO FLUIDO USATO) | COOLING FLUID SET POINT RANGE RANGE DEL SET POINT IMPOSTABILE [°C] | TANK VOLUME CAPACITA' SERBATOIO [Lt] | | STD FACTORY SET POINT STD SET POINT DI FABBRICA [°C] | |
| WATER + GLYCOL 20% | 13 ... 35 | 10 | | 18 | |
| TYPE OF PUMP (TIPO DI POMPA) | NOMINAL FLOW RATE (PORTATA NOMINALE) [L/min] | NOMINAL PRESSURE (PRESSIONE NOMINALE) 50 Hz [bar] | | NOMINAL PRESSURE (PRESSIONE NOMINALE) 60 Hz [bar] | |
| PERIPHERICAL/PERIFERICA | 10 | 2 | | 4,6 | |
| ELECTRICAL CIRCUIT (IMPIANTO ELETTRICO) | | | | | |
| POWER SUPPLY (ALIMENTAZIONE) [V / ph / Hz] | CONTROL CIRCUIT (CIRCUITO DI COMANDO) | ELECTRIC HEATER (RESISTENZA) [W] | | SCCR [kA] | |
| 230/1/50-230/1/60 | 24V AC | - | | 5 | |
| MAX POWER INPUT [kW] - CURRENT INPUT [A] (ASSORBIMENTI MASSIMI) | | | | | |
| 1,20 [kW] (50Hz) | | 1,40 [kW] (60Hz) | | | |
| 8 [A] (50Hz) | | 8 [A] (60Hz) | | | |
| SCHEMES (SCHEMI) | | HYDRAULIC DIAGRAM | ELECTRICAL DIAGRAM | | |
| | | 70006-235 | 70010-621 | | |
| INSTALLED FEATURES (OPZIONI INSTALLATE) | | | | | |
| CONFIGURATION HSP | | | | | |
| ACCESSORIES (EXTERNAL TO THE CHILLER, INSTALLATION BY CUSTOMER) ACCESSORI (INSTALLAZIONE ESTERNAMENTE AL CHILLER A CURA DEL CLIENTE) | | | INSTALLED FEATURES (OPZIONI INSTALLATE) | | |
| ACRONYM (ACRONIMO) | DESCRIPTION (DESCRIZIONE) | ELECTRICAL DIAGRAM | HYDRAULIC DIAGRAM | OTHER | DESCRIPTION (DESCRIZIONE) |
| | | BPG | BPG | | Hot-Gas By-pass |
| | | | BPH | | Hydraulic relief valve |
| | | EL | EL | | Electric Level |
| | | EM | | | Error message label |
| | | FS | FS | | Flow Switch |
| | | | | LTA-D | antivibration damper |
| | | | | LTA-E | lifting eyebolt |
| | | | | NFH | non ferrous hydraulic circuit |
| | | RCU | | | Remote control of unit |
| | | TD | TD | | Differential Thermostat |
| | | TE | | | Electronic Thermostat |
| | | TMN-TMX | | | Min-max temp. fluid alarm |
| | | | WT | | Water Unit |