

# PWI/PWS 6102

## ECOOL AIR/WATER HEAT EXCHANGER 1000 W

**PWI:** for partially recessed mounting in the door or side

**PWS:** for outer mounting on the door or side

- offers the highest degree of safety and energy efficiency
- cut-out compatible with ECOOL system e.g. for air/air heat exchanger and cooling units
- easy mounting with click and fit system for partially sunk-in version PWI
- maintenance-free
- integrated thermostat and solenoid valve for temperature control
- integrated temperature monitoring with alarm contact




PRODUCT		PWI 6102		PWS 6102		
ARTICLE NO.		12891401055	12891404055	12881401055	12881404055	Unit
<b>DATA</b>						
Rated voltage ±10 %		AC 50   60	AC 60	AC 50   60	AC 60	Hz
		230	115	230	115	V
Cooling capacity @ 200 l/h	W10/A35	1000				W
Power consumption	W10/A35	68   78	70	68   78	70	
Current consumption	W10/A35	0.3   0.34	0.6	0.3   0.34	0.6	A
Starting current	W10/A35	0.4	0.7	0.4	0.7	
Unimpeded airflow (free flow)	internal	520				m³/h
Pre fuse T		2				A
Type of connection	electro	spring-type terminal included with plug				
	fluid	13 mm hose nozzle   other connectors on request				
Noise level according to EN ISO 3741		≤ 48				dB (A)
Weight (without packaging)		10.5		11		kg
Ambient temperature range		> +1 ... +70   > +34 ... +158				
Control range (adjustable)		+8 ... +50   +47 ... +122; factory setting +35   +95				°C   °F
Water inlet temperature		> +2 ... +35   > +34 ... +95				
Permissible operating pressure		max. 10				bar
Duty cycle		100				%
Condensate management		condensate drain				
Protection system according to EN 60529	IP 55	towards the electrical enclosure if used as intended by the manufacturer				
Design	housing	galvanised steel   electrostatically powder coated (200 °C)   stainless steel on request				
	heat exchanger	copper pipe with aluminium fins   stainless steel piping on request				
Colour	cover	RAL 7035   different colours available on request				


ACCESSORIES	Piece	ARTICLE NUMBER
External condensate evaporation system	1	18314000001
Condensate bottle	1	18314000100

For additional models, options and voltages visit [www.pfannenberg.com](http://www.pfannenberg.com) or contact us directly.

### Cooling capacity performance curves



### Pressure loss performance curve



### Dimensions

PWI	X	Y	Z1	Z2	K	L
mm	380	615	82	60	577	350

PWI variants partially recessed by 60 mm after installation

PWS	X	Y	Z	A	B	C	D	E	F	G
mm	380	622.5	142	472	285	272	150	288	40	300

Mounting holes  $\varnothing$  8 mm and cut-out radii R20

PWI 6102	PWS 6102
----------	----------

