

# PWI/PWS 6152

## ECOOL AIR/WATER HEAT EXCHANGER 1500 W

**PWI:** for partially recessed mounting in the door or side

**PWS:** for outer mounting on the door or side

- offers the highest degree of safety and energy efficiency
- cut-out compatible with **ECOOL** system e.g. for air/air heat exchanger and cooling units
- easy mounting with click and fit system for partially sunk-in version PWI
- maintenance-free
- integrated thermostat and solenoid valve for temperature control
- integrated temperature monitoring with alarm contact




PRODUCT	PWI 6152			PWS 6152			
ARTICLE NO.	12892309055	12892301055	12892304055	12882309055	12882301055	12882304055	Unit

DATA		AC 50   60		AC 60	AC 50   60		AC 60	Hz
Rated voltage ±10 %		400	230	115	400	230	115	V
Cooling capacity @ 200 l/h	W10/A35	1500						W
Power consumption	W10/A35	77   76	91   122	91	77   76	91   122	91	A
Current consumption	W10/A35	0.35	0.47   0.54	0.79	0.35	0.47   0.54	0.79	
Starting current	W10/A35	0.6		0.9	0.6		0.9	m³/h
Unimpeded airflow (free flow)	internal	850						
Pre fuse T		2						A
Type of connection	electro	spring-type terminal included with plug						
	fluid	13 mm hose nozzle   other connectors on request						
Noise level according to EN ISO 3741		53						dB (A)
Weight (without packaging)		17	15	14.5	18	16	15.5	kg
Ambient temperature range		> +1 ... +70   > +34 ... +158						°C   °F
Control range (adjustable)		+8 ... +50   +47 ... +122; factory setting +35   +95						
Water inlet temperature		> +2 ... +35   > +34 ... +95						bar
Permissible operating pressure		max. 10						
Duty cycle		100						%
Condensate management		condensate drain						
Protection system according to EN 60529	IP 55	towards the electrical enclosure if used as intended by the manufacturer						
Design	housing	galvanised steel   electrostatically powder coated (200 °C)   stainless steel on request						
	heat exchanger	copper pipe with aluminium fins   stainless steel piping on request						
Colour	cover	RAL 7035   different colours available on request						


ACCESSORIES	Piece	ARTICLE NUMBER
External condensate evaporation system	1	18314000001
Condensate bottle	1	18314000100

For additional models, options and voltages visit [www.pfannenber.com](http://www.pfannenber.com) or contact us directly.

### Cooling capacity performance curves



### Pressure loss performance curve



### Dimensions

PWI	X	Y	Z1	Z2	K	L
mm	410	938	82	60	900	378

PWI variants partially recessed by 60 mm after installation

PWS	X	Y	Z	A	B	C	D	E	F
mm	410	945.5	142	662	320	350	280	282	55

Mounting holes  $\varnothing$  8 mm and cut-out radii R20

PWI 6152	PWS 6152
----------	----------

