

# PWS 7702

## AIR/WATER HEAT EXCHANGER 7000 W


- maintenance-free
- mounting-friendly seal, no elaborate reworking of the mounting cut-out
- integrated thermostat and solenoid valve for temperature control
- integrated temperature monitoring with alarm contact




PRODUCT		PWS 7702		
ARTICLE NO.		12057702055	12057710055	Unit
<b>DATA</b>				
Rated voltage ±10 %		AC 50   60		Hz
		400 3~	230	V
Cooling capacity @ 500 l/h	W10/A35	7000		W
Power consumption	W10/A35	530   770	520   680	A
Current consumption	W10/A35	1.39   1.39	2.4   3.2	
Starting current	W10/A35	3.3   3.3	9.2   12	
Unimpeded airflow (free flow)	internal	3630	4600	m³/h
Pre fuse T		10		A
Type of connection	electro	spring-type terminal included with plug		
	fluid	13 mm hose nozzle; other connectors on request		
Noise level according to EN ISO 3741		63		dB (A)
Weight (without packaging)		58		kg
Ambient temperature range		+1 ... +70   +34 ... +158		°C   °F
Control range (adjustable)		+8 ... +50   +47 ... +122; factory setting +35   +95		
Water inlet temperature		+1 ... +35   +34 ... +95		
Permissible operating pressure		max. 10		bar
Duty cycle		100		%
Condensate management		condensate drain		
Protection system according to EN 60529	IP 55	towards the electrical enclosure if used as intended by the manufacturer		
	IP 65	on request		
Design	housing	galvanised steel   electrostatically powder coated (200 °C)   stainless steel on request		
	heat exchanger	copper pipe with aluminium fins   stainless steel piping on request		
Colour	cover	RAL 7035   different colours available on request		
ACCESSORIES		Piece	ARTICLE NUMBER	
External condensate evaporation system		1	18314000001	
Condensate bottle		1	18314000100	

For additional models, options and voltages visit [www.pfannenber.com](http://www.pfannenber.com) or contact us directly.

### Cooling capacity performance curves



### Pressure loss performance curve



### Dimensions

PWS	X	Y	Z	A	B	C	D	E	F	G	H
mm	460	1800	310	525	910	210	65	442.5	433.5	410	350

Mounting holes  $\varnothing$  8 mm

### PWS 7702

